

# **OP175/50 SYSTEM**

## REVERSE OSMOSIS WATER TREATMENT SYSTEM WITH STORAGE TANK

#### System:

- OP175/50: 164-00225 Replacement Cartridges:
- CTO-Q10: 300-05828
- AMS-QT15: 204-52820
- MA-Q10: 300-05850



### **APPLICATIONS**

- Combi Ovens
- Steam Ovens

Proofers and Humidifiers

### **FEATURES • BENEFITS**

- Significantly reduces scale and corrosion problems related to high TDS, water hardness and chlorides
- Ideal for all applications where TDS, hardness and chloride reduction are necessary to meet manufacturer's warranty requirements
- Integrated mineral-addition cartridge provides TDS needed for conductivity sensors and optimal mineral content for all equipment applications
- High capacity pre-filters take out sediment and chlorine and protect the RO membrane

- Digital before-and-after TDS meter for push-button monitoring of membrane performance and optimized water quality
- Sample port allows quick and simple system checks and adjustments
- Integrated system bypass valve reduces service interruptions and down-time
- All consumables are easy tochange Qwik-Twist cartridges
- Built-in pressure gauge allows visual monitoring of operating pressure
- Simple, easy-to-install and service design

### **INSTALLATION TIPS**

- Feed water connection to system should be COLD only. Tempered water up to 80°F (26.6°C) can be used.
- Do not exceed system specifications for temperature and pressure.
- Provide a dedicated water line of at least 1/2" I.D. to the unit for consistent flow and pressure to the system.
- Allow 3" clearance below system for filter cartridge removal and replacement.
- Connect filtered water line to steam production connections only. Do not use for condenser and wash-water.
- Detailed installation, operation and maintenance manual are included with each system.

### **SIZING**

- Drain Connection: 2.0 gpm Minimum Flow
- Storage Tank Capacity: 50 gals.

### **OPERATION TIPS**

- Change cartridges on a regular six (6) month preventative maintenance program.
- Change cartridges when capacity is reached or when flow becomes too slow.
- Always flush the filter cartridge at time of installation and cartridge change.

# OP175/50 SYSTEM


### 164-00225

#### System:

- OP175/50: 164-00225

Replacement Cartridges:

- CTO-Q10: 300-05828
- AMS-0T15: 204-52820



The contaminants or other substances removed or reduced by this drinking water system are not necessarily in your water. Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.

26.5

Since the conditions under which our products may be used are beyond our control, we cannot accept any liability with respect to the improper installation. application and/or use of our products.

For Pentair® Everpure® Product Warranties visit: http://pentair.com/assets/foodservice-warranty

# **PENTAIR**

### **SPECIFICATIONS**

- Service Flow Rate Up to 4 gpm (15 Lpm) at 50 psi
- Daily Production Rate  $175 \text{ gpd} (633 \text{ Lpd}) \text{ at } 77^{\circ}\text{F} (25^{\circ}\text{C}), 60 \text{ psi}$ (4.1 bar) feed water pressure. Production will vary based on water supply temperature and pressure
- **Storage Tank Capacity** 50 gallons (189.27 L)
- Drain Connection Minimum 2.0 gpm (7.6 Lpm)
- **Pressure Requirements** 60 - 85 psi (3.5 - 5.9 bar), non-shock
- Inlet Water Temperature  $40 - 100^{\circ} F (4 - 38^{\circ} C)$
- Overall Dimensions Processor:

20.4" H x 19.5" W x 8.4" D 51.8 cm x 49.5 cm x 21.3 cm

51.5" H x 26.5" Dia. 130.81 cm x 67.31 cm Dia.

### **Options**

	Model	Description	Part No
	Air-Gap Kit	Air-Gap Approved for drain line	164-89905
	BPA200	Booster Pump Assy	164-85015
	QTPTCR-10-1	QT Chloramine Reduction System	160-52085
	PRV	Pressure Reducing Valve	164-89938
	QTPT-1	CTO Post-Treatment	160-52120
	Remote Kit	Repressurization/ Storage Tank Assembly remote kit	164-89116

- Inlet Connection 3/8" Push fit tubing
- Outlet Connection 1/2" I.D. hose
- Shipping Weight 125 lbs (56.7 kgs)
- Electrical Connection Repressurization Pump: 120 VAC / 60 Hz / 2 Amps Storage Tank: 120 V

eed TDS	Up to 1200 ppm
eed pH	6-10 units
Hardness*	12 grains or less
ree Chlorine	<2 mg/L
ron	0.1 mg/L max
Гurbidity	0.50 NTU
1anganese	0.05 mg/L max
Hydrogen Sulfide	0.00 mg/L

Pentair Customer Service

### Replacement Media

Model	Qty	Description	Part No
CTO-Q10	2	Pre-Filter	300-05828
AMS-QT15	1	Membrane	204-52820
MA-Q10	1	Post-Filter	300-05850

It is recommended that pre/post-filters and mineral addition cartridges are changed every six (6) months, when capacity is reached or when feed water pressure or flow becomes inadequate.

United States | 1040 Muirfield Drive | Hanover Park, IL 60133 | 800.942.1153 (US Only) 630.307.3000 Main | cseverpure@pentair.com | foodservice.pentair.com Australia | 1-21 Monash Drive | Dandenong South, Vic 3175 | Australia | 011.1300 576 190 Tel | au.everpure@pentair.com

China | 21F Cloud 9 Plaza, NO 1118 | Shanghai, 200052 | China | 86.21.3211.4588 Tel | china.water@pentair.com

India | Boulevard, B-9/A, 7th Floor - Tower B Sector 62 | Noida - 201301 | 91.120.419.9444 Tel | indiacustomer@pentair.com

Europe | Pentair Water Belgium BVBA | Industriepark Wolfstee, Toekomstlaan 30, B-2200 Herentals | Belgium | +32.(0).14.283.504 Tel | sales@everpure-europe.com Japan | Japan Inc. | Hashimoto MN Bldg. 7F, | 3-25-1 Hashimoto, Midori-ku, Sagamihara-shi | Kanagawa 252-0143 | Japan | 81.(0)42.775.3011 Tel | info@everpure.co.jp Southeast Asia | 390 Havelock Road, | #04-01 King's Centre | Singapore 169662 | 65.6768.5800 Tel | cseverpure@pentair.com

All indicated Pentair trademarks and logos are property of Pentair. Third party registered and unregistered trademarks and logos are the property of their respective owners Because we are continuously improving our products and services, Pentair reserves the right to change specifications without prior notice. Pentair is an equal opportunity employer.

©2021 Pentair. All Rights Reserved. 164-00225 JL21